



Main

Device short name	C
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body Material	Zinc alloy
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Number of connectors	1 x Orange 2 x Red 3 x White 4 x Black 1 x ground connection) Green
Switch actuation	CW and CCW
Tilting angle	45 °
Torque Value	3 lbf.in (0.34 N.m)
Connector type	5 pins mini

Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Product Certifications	UL Listed CE CSA

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901012498
Nbr. of units in pkg.	1
Package weight(Lbs)	20.00 oz (566.991 g)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.16 in (25.806 cm)
Package 1 width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile