# Precision Test Adapters

## 1.85 mm(M) to 1.85 mm(M): Right Angle type



**Withwave's Precision Test Adapters** are designed based on precision microwave interconnection technologies.

This 1.85 mm(M) to 1.85 mm(M) *Right Angle adapter* is manufactured to precise microwave specifications and constructed with male gender on both side.

The precision microwave connector interfaces ensure an excellent microwave performance up to 67 GHz



#### Features

- Frequency range : DC to 67 GHz

- VSWR(Max): 1.30:1

- Body: Stainless steel (passivated)

### Specification

Scope	Specification	AD01M01MR1
Electrical	Impedance(Ohm)	50
	Operation Freq.(GHz)	DC to 67 GHz
	VSWR (Max)	1.30 : 1
Material	Dielectric	PTFE
	Center Contact	Brass with gold plated
	Body	Passivated Stainless Steel

<sup>\*</sup> RoHS Compliant


# Precision Test Adapters



## 1.85 mm(M) to 1.85 mm(M): Right Angle type

### Drawing

Part No.: AD01M01MR1 Unit : mm[inch]



#### Test Result

■ Frequency: 10 MHz to 67 GHz

