

FLH.01.250.DLAE31

SUMMARY

Wires

Series	01	
Termination type	Male solder	
IP rating	50	
AWG wire size	0.00 - 0.00	
Cable Ø	0.00 - 0.00 mm	
Status	Active	

1



Image is for illustrative purpose only

Download			
Request a quote			
Catalog			

TECHNICAL DETAILS

Mechanics

Shell Style/Model	FLH.01*: Elbow plug, non-latching, for cable crimping	
Keying	Circular, male	
Housing Material	Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces	
Weight	2.10 g	

Performance

Configuration01.250 : 1 Coax (50 Ohm)InsulatorRated Current

Specifications


Contact Type: Solder

Others

Endurance (Shell): 1000 mating cycles

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS





Dimensions

	А	н	L
mm.	6	14.5	11
in.	0,24	0,57	0,43

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.