MALLORY Mallory Sonalert Products, Inc. Part #: SCE016XD2DP2B **Sales Outline Drawing** Revision: Specifications: Sound Level Category: Extra Loud Mode of Operation: Fast Double Pulse @ 2 Pulse Rate (PPS): Loudness @ 2 FT: 95 to 105 dB(A) Typ. 2000 ± 500 Hz Frequency: Connection: Voltage Rating: 6 to 16 VDC **Current Draw:** 40mA MAX Housing Material: 6/6 Nylon, Color: Black Storage Temperature: -40° to +85° C **Operating Temperature** -40° to +85° C Panel Mounting: Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. Knurled Nut: Used to attach part to panel. The max recommended torque is 10 in-lbs. Weight (Typical): 2.1 oz (60g) NEMA 3R,4X, & 12: Approved with use of ACC03. cUL Recognition: cUL Recognized Options: Please contact factory.

Dimensions: Inches (mm)

ROHS Compliant

