

Oct.1.2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C	
	OPERATING&STORAGE HUMIDTY RANGE	85%MAX	APPLICABLE CABLE	△ CABLE DIAMETER : φ7.3~9.3	
	VOLTAGE		CURRENT		
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.			X	X
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△	1	DIS-E-00003216	KN. ICHIKAWA	TU. TANIGUCHI	20201019
REMARK			APPROVED	KN. ICHIKAWA	20100705
THIS PRODUCT SHALL BE MATED WITH DH40-37S OR DH3 * B-37S, IT APPLIES TO DH40-37S OR DH3 * B-37S ABOUT A MECHANICAL, ENVIRONMENTAL CHARACTERISTICS.  Unless otherwise specified, refer to IEC 60512.			CHECKED	KN. ICHIKAWA	20100705
			DESIGNED	TU. TANIGUCHI	20100705
			DRAWN	TU. TANIGUCHI	20100705
			Note QT:Qualification Test AT:Assurance Test X:Applicable Test		
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	DH-37-CV2B	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL244-0015-9-00	△ 1/1