

## SUMMARY

### # Wires

Coax 1



*Image is for illustrative purpose only*

Series 00  
Termination type Female solder  
IP rating 50  
AWG wire size 0.00 - 0.00  
Cable Ø 2.30 - 2.70 mm  
Status Active  
Matching parts [FLA.00.250.CLAC27Z](#)

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model PCA\*: Free receptacle with cable collet  
Keying Circular, female  
Housing Material Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces  
Variant Z : Nut for fitting a bend relief  
Weight 4.26 g

### Performance

Configuration 00.250 : 1 Coax (50 Ohm)  
Insulator L: PEEK (UL 94 / V-0/1.5)  
Rated Current 4 Amps

### Specifications

Contact Type: Coaxial 50 Ohm (Solder)  
Contact Dia.: 0.7 mm (0.028in)  
Bucket Dia.: 0.6 mm (0.024in)  
Test voltage: 2.1 kV (rms)  
R (max): 6.1 mOhm  
Vtest: 2100 V (AC), 3000 V (DC)

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*


□  
Impedance: 50 Ohm  
VSWR:  $1.09 + 0.11 * f/\text{GHz}$   
Cable type: RG 316 /U

## Others

Endurance (Shell): 5000 mating cycles  
F ret (min): 100 N  
Salt Spray Corrosion: >1000 hr

---

## DRAWINGS



## Dimensions

|     | A    | L    | S2   |
|-----|------|------|------|
| mm. | 6.5  | 32.5 | 6    |
| in. | 0,26 | 1,28 | 0,24 |

---



## RECOMMENDED BY LEMO

### Tools

Spanner wrench: [DCD.00.ZZZ.PA060](#)

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

## Cables

|                    |           |       |                                                                                    |
|--------------------|-----------|-------|------------------------------------------------------------------------------------|
| 17450              | COPOLYMER | Black |  |
| 18700              | PTFE      | White |  |
| 18800              | PTFE      | White |                                                                                    |
| CCX.50.RG0.58AU14B | FEP       | White |                                                                                    |
| CCX.50.RG1.74-U25N | PVC       | Black |                                                                                    |
| CCX.50.RG1.74U25N  | PVC       | Black |                                                                                    |
| CCX.50.RG1.88AU24B | TFE       | White |                                                                                    |
| CCX.50.RG1.88AU26B | PFA       | White |                                                                                    |
| CCX.50.RG1.88AU26B | PTFE      | White |                                                                                    |
| CCX.50.RG3.16BU26M | FEP       | Brown |                                                                                    |
| CCX.75.RG1.79BU26M | FEP       | Brown |                                                                                    |
| CCX.75.RG1.87AU26B | PFA       | White |                                                                                    |
| CCX.75.RG1.87AU27B | PTFE      | White |  |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.