

# 20 dB Fixed Attenuator, 4.3-10 Male to 4.3-10 Female Aluminum Body Rated to 15 Watts Up to 6 GHz



## **RF Fixed Attenuators Technical Data Sheet**

PE7AP1001-20

### **Features**

- Bidirectional
- DC to 6 GHz Frequency Range
- Attenuation 20 dB ± 0.3 dB

- Max Power 15 Watts (CW)
- VSWR < 1.15:1</li>

## **Applications**

- Instrumentation
- · Precision measurements
- Prototyping and characterization
- · Production systems

### **Description**

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 20 dB Fixed Attenuator PE7AP1001-20 is rated to 15 Watts and operates from DC to 6 GHz. The versatile coaxial package uses 4.3-10 male to 4.3-10 female connectors and is also REACH and RoHS compliant.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
Nominal Attenuation		20		dB
Attenuation Accuracy			±0.5	dB
VSWR			1.15:1	
Input Power, CW			15	Watts
Input Power, Peak			250	Watts
1 µs, 1%				

# Mechanical Specifications Size

Body Material and Plating Aluminum Finish Anodized

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 20 dB Fixed Attenuator, 4.3-10 Male to 4.3-10 Female Aluminum Body Rated to 15 Watts Up to 6 GHz PE7AP1001-20

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



# 20 dB Fixed Attenuator, 4.3-10 Male to 4.3-10 Female Aluminum Body Rated to 15 Watts Up to 6 GHz



# **RF Fixed Attenuators Technical Data Sheet**

PE7AP1001-20

Configuration

Design Fixed

Package Style Connectorized

#### Connectors

Description	Connector 1	Connector 2	
Туре	4.3-10 Male	4.3-10 Female	
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold over Nickel	
Dielectric Type	PTFE	PTFE	
Outer Conductor Material and Plating	Beryllium Copper, Silver	Beryllium Copper, Silver	
Body Material and Plating	Brass, Nickel	Brass, Nickel	

#### **Environmental Specifications**

**Temperature** 

Operating Range -40 to +85 deg C Storage Range -40 to +85 deg C

Ingress Protection (IP) Rating IP67

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 20 dB Fixed Attenuator, 4.3-10 Male to 4.3-10 Female Aluminum Body Rated to 15 Watts Up to 6 GHz PE7AP1001-20

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451




# 20 dB Fixed Attenuator, 4.3-10 Male to 4.3-10 Female Aluminum Body Rated to 15 Watts Up to 6 GHz



### **RF Fixed Attenuators Technical Data Sheet**

PE7AP1001-20



20 dB Fixed Attenuator, 4.3-10 Male to 4.3-10 Female Aluminum Body Rated to 15 Watts Up to 6 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 20 dB Fixed Attenuator, 4.3-10 Male to 4.3-10 Female Aluminum Body Rated to 15 Watts Up to 6 GHz PE7AP1001-20

URL: https://www.pasternack.com/20db-fixed-4.3-10-male-4.3-10-female-15-watts-attenuator-pe7ap1001-20-p.aspx

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

# PE7AP1001-20 CAD Drawing

20 dB Fixed Attenuator, 4.3-10 Male to 4.3-10 Female Aluminum Body Rated to 15 Watts Up to 6 GHz

