

Sales Outline Drawing

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

| | |
|----------------------------------|--|
| Resonant Frequency (Hz) | 2500 ± 1000 |
| Operating Voltage (Vdc) | 5 ~ 15 |
| Rated Voltage (Vdc) | 12 |
| Current Consumption (mA/max) | 150 at Rated Voltage |
| Sound Pressure Level (dB/min) | 110 at 100cm at Rated voltage |
| Tone/Pulse Rate (Hz0) | Sweep 3.3 ±20% |
| Operating Temperature (°C) | -20 ~ +70 |
| Storage Temperature (°C) | -30 ~ +80 |
| Housing | ABS 757 UL94HB plastic resin (Color: Black) |
| Lead Wire | 20 AWG |
| Weight (Grams) | 79.2 |
| Condition by wave soldering (°C) | 245 ±5 / 3±0.5 sec |
| Condition by hand soldering (°C) | 350 ±20 / within 5 sec |
| Options | For other options contact factory |

Dimensions: (units: mm)

PS: Vp-p = 1/2duty, square wave

ROHS Compliant

