



Click [here](#) for the 3D model.

Dimensions

L	3mm +/-0.1mm
W	3mm +/-0.1mm
T	1.2mm MAX

Packaging Specifications

Packaging	T&R
Packaging Quantity	2000

General Information

Series	L-DWD
Style	SMD
Chip Size	3012(1212)
Description	Shielded, Surface Mount Inductor
Features	Low Profile
RoHS	Yes
Notes	Last Order Date June 30, 2023. Suggested Replacement - https://productfinder.pulseelectronics.com/part/BWVFO0303012470M00 .

Specifications

Inductance	47 uH
Inductance Tolerance	20%
Temperature Range	-25/+120°C
Shielded	Yes
Current	250 mAmps (MAX), 280 mAmps (Self Heating)
DC Resistance	1.45 Ohms
Self-Resonant Frequency	17 MHz MIN