MALLORY Mallory Sonalert Products,Inc. Part #: SCE048LD3VC4B Revision: **Sales Outline Drawing** Α Specifications: Sound Level Category: Loud Medium Soft Mode of Operation: Slow Pulse Slow Pulse Slow Pulse Pulse Rate (PPS): 75 to 85 dB(A) Typ. 65 to 75 dB(A) Typ. Loudness @ 2 FT: 85 to 95 dB(A) Typ. Frequency: 2900 ± 500 Hz 2900 ± 500 Hz 2900 ± 500 Hz T-BLOCK; BLUE WIRE T-BLOCK; YELLOW Connection: T-BLOCK ONLY WIRE TO (-) TO (-) Voltage Rating: 28 to 48 VDC **Current Draw:** 40mA MAX Housing Material: 6/6 Nylon, Color: Black Storage Temperature: -40° to +85° C -40° to +85° C **Operating Temperature** Panel Mounting: Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. Knurled Nut: Used to attach part to panel. The max recommended torque is 10 in-lbs. Weight (Typical): 1.6 oz (45g) NEMA 3R,4X, & 12: Approved with use of ACC03. cUL Recognition: cUL Recognized Options: Please contact factory. **ROHS Compliant** Dimensions: Inches (mm) YELL D\ **BLUE** ONALER) MAUDRY

