		ТОР	VIEW	SIDE VI	EW					
		023		Silk Screen Marking "LF X/X" Date Code Marking "6 A" Year J L Month 6=2006 A=Jan. 9.8±0.3	2-Ø0.8±0	1				
Specifications			Notes		Revision History					
Description	Value	Unit		Notes	Version		Description		Date	Approved
Technology	Piezo		1) All dimensions are in mm unless otherwise noted		1	Released from Engineering			10/21/2013	J.S
Resonant Frequency	4,800	(Hz)	All parts meet RoHS							
Rated Voltage	12	(V)								
SPL @ 10cm	85	(dBA)								
Capacitance	15,000	(pF)								
Mount Type	Thru-hole									
Voltage Range	1~40	(V)								
Max Rated Current	7	(mA)								
Housing Material	207				Drawn by	Date	Checked by	Date	Approved by	
	PBT								Approved by	Date
Operating Temperature	-20 ~ +60	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	Date 10/21/2013
Operating Temperature Storage Temperature		°C °C		Piezo Transducer	A.B.	10/21/2013	C.E.		J.S	

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.