## Part #: MALLORY Mallory Sonalert Products,Inc. ZT028LAIC2G Sales Outline Drawing Revision: E INDIVIDUAL CONTROL OF LIGHT AND SOUND **Specifications:** Function LIGHT SOUND Sound Level Category N/A Loud Mode of Operation Fast Pulse @ 10 PPS Continuous

Opaque White	N/A
GREEN	N/A
24 VAC/DC	24 VAC/DC
20 to 28 VAC/DC	20 to 28 VAC/DC
L~ to ~VAC/DC	S~ to ~VAC/DC
25mA MAX	25mA MAX
N/A	3900 ± 500 Hz
N/A	85 to 95 dB(A) Typ.
6/6 Nylon, Color: Black	
6/6 Nylon, Color: Opaque White	
-40° to +80° C	
	GREEN  24 VAC/DC  20 to 28 VAC/DC  L~ to ~VAC/DC  25mA MAX  N/A  N/A  6/6 Nylon, 6/6 Nylon, Colo

Operating Temperature

Panel Mounting

Recommended hole size is 22.5 mm. Thread front will fit standard 22.5mm hole.

Knurled Nut

Used to attach part to panel. The max recommended torque is 10 in-lbs.

Weight (Typical)

NEMA 3R.4X, & 12

Osed to attach part to panel. The max recommended torque is 10 in-ib.

Approved with use of included gasket.

Options Please contact factory.

