



used for: D-SUB

PRODUCT NO.	
SHORT SCREW	LONG SCREW
9 300X11129X	300X11179X
15 300X11139X	300X11189X
25 300X11149X	300X11199X
37 300X11159X	300X11209X
50 300X11169X	300X11219X

Directive 2002/95/EC
RoHS
Compliant

POS.	A	B	C	D	E	F	G
9	19.8	25.0	31.0	47.0	15.6	---	8.5
15	27.9	33.3	40.2	48.3	16.2	---	10
25	41.5	47.0	53.7	48.8	16.2	---	11
37	57.8	63.5	69.0	48.5	16.2	20.8	14
50	55.0	61.1	67.0	48.5	18.7	23.2	15

finish: ZINC PLATED

tolerance: 2:1

scale: material: title: METALHOOD 9-50 pos.

1995 date name 1995 date name
drawn 03.07. Barcinski
appd. 03.07. Mickenbecker
norm
d-old

dwg no: 16V1107A [CAD/ REL.14 DIN-A 3
sh:1/1

product no: SEE TABLE

DO NOT ALTER CAD DRAWING BY HAND
OWNERSHIP AND COPYRIGHT OF CONEC GMBH
WRITTEN PERMISSION.
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT

THIS DRAWING MAY NOT BE COPIED OR

CONEC®