

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com









The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

### **General ordering data**

Version	HDC enclosures, Size: 12, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: M 50
Order No.	<u>1983510000</u>
Туре	HDC 48B SDLU 2M50G
GTIN (EAN)	4032248687770
Oty.	1 pc(s).



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Technical data**

### **Dimensions and weights**

Depth	143 mm	Depth (inches)	5.63 inch
Height	120 mm	Height (inches)	4.724 inch
Width	166.2 mm	Width (inches)	6.543 inch
Mounting dimension - height	106 mm	Mounting dimension - width	111 mm
Net weight	1,445 g		

#### **Temperatures**

Limit temperature -40 °C ... 125 °C

### **Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1	Lead 7439-92-1		
SCIP	d447edfa-0214-4f34-b5ba-82eae491b46a			
Chemical resistance	Substance	Acetone		
	Chemical resistance	Conditionally resistant		
	Substance	Drilling oil		
	Chemical resistance	Resistant		
	Substance	Diesel		
	Chemical resistance	Resistant		
	Substance	Ethyl alcohol		
	Chemical resistance	Resistant		
	Substance	Transmission oil		
	Chemical resistance	Resistant		
	Substance	Hydraulic oil		
	Chemical resistance	Resistant		
	Substance	Coolant		
	Chemical resistance	Resistant		
	Substance	Petroleum benzine		
	Chemical resistance	Resistant		
	Substance	Sweat		
	Chemical resistance	Resistant		
	Substance	Premium gasoline		
	Chemical resistance	Conditionally resistant		
	Substance	Water		
	Chemical resistance	Resistant		
	Substance	UV		
	Chemical resistance	Unstable		
	Substance	Ozone		
	Chemical resistance	Unstable		

### **Dimensions**

Cable entry	w. thread	Height of base B1	10 mm
Height of housing B	120 mm	Hole pitch length A2	111 mm
Total length housing	132 mm	Width base C1	120 mm
Width housing C	90 mm		



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Technical data**

### **General data**

EMC housings	No	Housing main material	diecast aluminium
Material of locking element		Protection class note	Protection class with
	Stainless steel, rust-proof		secured cover: IP 65
Protection degree	IP65 (in plugged	Surface finish	
	condition)		Powder coating
Tightening torque	1.2 Nm		

### Version

BG	12	Cable entry	w. thread
Clamp version	End-locking clamp	Colour (RAL)	RAL 7035
Cover	with cover	Design	Standard
Design of cover	with cover	Design of housing	Base housing
Design of locking system	End-locking clamp, lower side	Internal thread	M 50
Number of cable entry on top	0	Number of cable entry sideways	1
Sealing	NBR	Size	12
Size of cable entries	M 50	Suitable for ModuPlug <sup>®</sup>	Yes
Tightening torque	1.2 Nm	Top part/bottom part/lid	lower part
Туре	Base housing		

### **Classifications**

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

### **Approvals**

Approvals



ROHS	Conform
------	---------

### **Downloads**

Engineering Data	CAD data – STEP
Engineering Data	<u>EPLAN</u>
Product Change Notification	20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen
Catalogues	Catalogues in PDF-format
Brochures	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Drawings

