



N=Number of contacts



PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL  
 INSULATOR: PA 66  
 FLAMABILITY RATING: UL94-V0  
 COLOR: GREEN  
 CONTACT: BRASS  
 SOLDER TAIL PLATING: TIN  
 FLANGES SCREW NUT: BRASS M2.5

ENVIRONMENTAL  
 OPERATING TEMPERATURE: -40 UP TO 105°C  
 COMPLIANCE: LEAD FREE AND ROHS

|                       |             |        |
|-----------------------|-------------|--------|
| ELECTRICAL            | cULus       | VDE    |
| CURRENT RATING:       | 10A         | 10.5A  |
| WORKING VOLTAGE:      | 300VAC      | 300VAC |
| WITHSTANDING VOLTAGE: | 1.6KV       | 2.5KV  |
| CONTACT RESISTANCE: □ | 20 mOhm max |        |

STANDARD  
 CERTIFIED E315414 / MODEL NUMBER 3233  
 CERTIFIED 40023195 / MODEL NUMBER 3233

MECHANICAL  
 PITCH: 3.81MM

SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

SERIE 3233

RoHS Compliant

|     |           |          |    |
|-----|-----------|----------|----|
| G   |           |          |    |
| F   |           |          |    |
| E   |           |          |    |
| D   |           |          |    |
| C   |           |          |    |
| B   | 12-OCT-09 | STANDARD | JP |
| A   | 31-OCT-08 | PDF      | JP |
| REV | DATE      | FILE     | BY |

|              |  |
|--------------|--|
| PROJECTION:  |  |
| APPROVAL: RJ |  |

|                   |
|-------------------|
| GENERAL TOLERANCE |
| .X = +/- 0.2      |
| .XX = +/- 0.15    |
| UNIT: MM          |
| SCALE:            |
| SHEET: 1/1        |
| DRAW: MARVIN      |

|   |                              |
|---|------------------------------|
| DESCRIPTION: SERIE 3233 - 3.81MM VERTICAL PCB HEADER WITH FLANGES | <b>SIZE</b><br><br><b>A4</b> |
| WR-TBL  |                              |
| WERI PART NO: 691 323 300 0xx                                     |                              |

A

B

C

D