



## Main

Product range	8501N
Product type	Relay Socket
Pin shape	Spade
Number of pins	14
[In] rated current	10 A 300 V AC

## Complementary

Electrical connection	Double tiered screw clamp terminals
Mounting type	Panel DIN rail
Package quantity	1

## Environment

Certifications	UL Recognized CSA CE
Height	2.74 in (69.6 mm)
Width	1.98 in (50.3 mm)
Depth	1.09 in (27.7 mm)

## Ordering and shipping details

Category	21142 - 8501 N
Discount Schedule	CP2
GTIN	785901137313
Nbr. of units in pkg.	1
Package weight(Lbs)	2.72 oz (77.111 g)
Returnability	Yes
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.80 in (7.112 cm)
Package 1 width	1.10 in (2.794 cm)
Package 1 Length	2.00 in (5.08 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	28.00 oz (793.786 g)
Package 2 Height	1.90 in (4.826 cm)
Package 2 width	5.30 in (13.462 cm)
Package 2 Length	6.40 in (16.256 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------