

т	۵	п –	m	0







LAYOUT SHOWN AS

Keying Shown as example

## CHARACTERISTICS

ယ

 $\sim$ 

-Mass

BASIC SERIES:

SHELL SIZE : 11

SHELL TYPE : Square Flange Receptacle

PLATING : Z = Black Zinc Nickel

Н

CONTACT TYPE : Standard Crimp Contact

-Standard : Based on MIL-DTL-38999 Series III

ł	-Shell Material	: Aluminium			
	-Shell Plating	: Black Zinc Nickel			
	-Insulator	: Thermoplastic			
	-Contacts	: Copper Alloy			
	-Seals & Grommet	: Silicon Elastomer			
	-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum			
	-Durability	: 500 Mating cycles			
	-Delivered with Souriau contacts and Accessories				
	-Temperature Range	-65℃ to +175℃			
	-Salt Spray	: 500 hours			

: 13.92 g ± 10%

8D 0

G

11

Ζ

22

В

F

Ν


Dim	Nominal	
Р	3.25±0.2	
PP	4.93±0.2	
R1	20.62	
R2	18.26	
S	26.2±0.3	
V	20.83+0/-1.25	
W	2.1/2.5	
Z	31.5 Max	
VV THREAD	M15x1-6g	


ORIENTATION : N

CONTACT LAYOUT : 11-22

CONTACT TYPE : SOCKET(500 Matings)

Е





	σ		A			
		I.				
					4	
	60					
7		1				
		1				
S FX/	AMPLE				3	
	non-conformit					
er of t	which does not comply with of the Parties or by a third party					
ndatio	on, technical n	otice.)				
untry FR	Jurisc	liction & Cont Not Listed	rol List		2	
		Not Listed		]	2	
1Z22BN						
				1		
				MOD N°		
		CUSTOMER	R DRAWING			
um	Receptac	e 8D seri	es			
	n Receptacle 8D series					
ar :			PROJECT 59			
	This document is the property of					
SOURIAU it must not be reproduced or						
	communicated without permission					
	DRG N°			SHEET		
.22	2BN-C		٨	1/2	J	
	В	I	A			

4	(	Contact Layout 22*			A	SQUARE FLANGE RECEPTACLE (TYPE 0)
_		4#22D 11-22	]		<u>ک</u>	
ω	Ctc A B C D	X Y   1.905 1.905   1.905 -1.905   -1.905 -1.905   -1.905 1.905				Dim ØA ØAA R1 ØT
						SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recomment
N						PN: 8D01
_					A 08-10-20 ISS DATE Designed By:	016 First Release
-					SCALE NA	Aluminiu General linear Tolerances:
					FORMAT A3	U WWW.SOURIAU SOURIA 8D011
	Н	G	F	E	D	C

Т

ш

т

G

0

