

Ŧ	۵	н п	m	0







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

-Salt Spray

BASIC SERIES:

SHELL SIZE : 19

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : J = Olive drab Cadmium

ယ

 \sim

-Standard : Based on MIL-DTL-38999 Series III

-Shell Material	: Composite		
-Shell Plating	: Olive drab Cadmium		
-Insulator	: Thermoplastic		
-Contacts	: Copper Alloy		
-Seals & Grommet	: Silicon Elastomer		
-Contact Plating	: Gold over copper Alloy 0.8µm minimum		
-Durability	: 500 Mating cycles		
-Delivered with Souriau contacts and Accessories			
-Temperature Range	<u>-</u> -65°C to +175°C		

: 2000 hours

8D 0

G

19

J

18

А

F

А


Connector dimension				
Dim	Nominal			
Р	3.25±0.2			
PP	4.93±0.2			
R1	29.36			
R2	26.97			
S	36.5±0.3			
V'	19.5+1.4/-0			
W'	2.1/3.65			
Ζ'	32 Max			
VV THREAD	M28x1-6g			


ORIENTATION : A

CONTACT TYPE : PIN(500 Matings)

Е

CONTACT LAYOUT : 19-18





	Ξ	I	A				
1					4		
S EXA	EXAMPLE						
whic er of t	non-conformit h does not co he Parties or t n, technical n Jurisd	mply with by a third par			2		
.9J1	L8AA			MODIN			
		CUSTOME	R DRAWING	MOD N°	 		
ite	ite Receptacle 8D series						
ar	NPRDS / PROJECT 859						
				erty of	1		
	.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission						
U DRG N° SHEET							
)J18	BAA-C			1/2	J		
	В		A				

