



Date	SYM	REVISION RECORD	AUTH	DR.	CK.
07/07/17	C	UPDATED NOTES	T.B.	B.S.	
03/26/19	D	UPDATED TO "ROHS COMPLIANT"	T.B.	B.S.	




**NOTES:**

- Plastic material - Polypropylene
- Flammability Rating -UL94-HB, UL File NO. E216959
- Temperature Range: -10°C to +100°C
- Springs - Nickel Plated Spring Steel
- Rivets - Brass, Nickel Plated
- Lugs: Brass, Nickel Plated
- CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER EIA-540J000
- ROHS COMPLIANT

**Mounting Instruction:**

Use 2-56 machine screws or eyelets 0.089" OD by 0.15" flange stimpson GS-3 series or equivalent. also adhesives and double sided tapes work well.

Tolerance (Except as noted)	 <b>Memory Protection Devices, Inc</b> 200 Broad Hollow Road, Farmingdale, New York 11735		
	decimal ±.5 (.020)	Scale	Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title ONE "AAA" CELL HOLDER WITH SOLDER LUGS		
Angular ± 3°	Date 03/26/19	Drawing Number BCAAAL	