MALLORY Mallory Sonalert Products,Inc. Part #: SCE016LD2VC1B Revision: **Sales Outline Drawing Specifications:** Sound Level Category: Loud Medium Soft Mode of Operation: Continuous Continuous Continuous Loudness @ 2 FT: 85 to 95 dB(A) Typ. 75 to 85 dB(A) Typ. 65 to 75 dB(A) Typ. Frequency: 2000 ± 500 Hz 2000 ± 500 Hz 2000 ± 500 Hz T-BLOCK; BLUE WIRE T-BLOCK; YELLOW T-BLOCK ONLY Connection: WIRE TO (-) TO (-) 6 to 16 VDC Voltage Rating: Current Draw: 40mA MAX Housing Material: 6/6 Nylon, Color: Black Storage Temperature: -40° to +85° C Operating Temperature -40° to +85° C Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. Panel Mounting: Knurled Nut: Used to attach part to panel. The max recommended torque is 10 in-lbs. Weight (Typical): 2.1 oz (60g) NEMA 3R,4X, & 12: Approved with use of ACC03. cUL Recognition: cUL Recognized Options: Please contact factory. **ROHS Compliant** Dimensions: Inches (mm) - BLUF YELL DW-ONALER) 1.210 1.240

