## CTDLW21SHQF Series

## From 50 $\Omega$ to 120 $\Omega$



## **CHARACTERISTICS**

Description: SMD Common Mode Choke.

**Applications:** USB line for personal computers and peripherals, DVC, STB and LVDS, panel line for liquid display panels, HDMI, DVI, Display port, etc.

**Operating Temperature:** -40°C to +105°C (includes self temp. rise)

Impedance Tolerance: ±25%


**Testing:** Impedance is tested on an HP4287A at 100MHz. **Packaging:** Tape & Reel.

**Miscellaneous: RoHS Compliant.** Other values available. **Additional Information:** Additional electrical & physical information available upon request.

Samples available. See website for ordering information.

| SPECIFICATIONS<br>Impedance tolerance ±25%               |                  |                        |                     |                           |                      |                                       |  |  |  |
|--|------------------|------------------------|---------------------|---------------------------|----------------------|---------------------------------------|--|--|--|
| Part<br>Number   | Impedance<br>(Ω) | Test<br>Freq.<br>(MHz) | IDC<br>Max.<br>(mA) | Rated<br>Voltage<br>(VDC) | DCR<br>Max.<br>(Ω)   | Insulation<br>Resistance<br>Min. (ΜΩ) |  |  |  |
| CTDLW21SHQF-500P<br>CTDLW21SHQF-670P<br>CTDLW21SHQF-900P | 50<br>67<br>90   | 100<br>100<br>100      | 500<br>500<br>330   | 50<br>50<br>50            | 0.20<br>0.30<br>0.35 | 10<br>10<br>10                        |  |  |  |
| CTDLW21SHQF-121P   | 120              | 100                    | 330                 | 50                        | 0.35                 | 10                                    |  |  |  |

| PHYSICAL DIMENSIONS |             |            |             |      |       |  |  |  |  |  |
|---------------------|-------------|------------|-------------|------|-------|--|--|--|--|--|
| Size                | Α           | В          | C           | D    | E     |  |  |  |  |  |
| mm                  | 2.05±0.2    | 1.25±0.2   | 1.20±0.2    | 0.50 | 0.58  |  |  |  |  |  |
| inches              | 0.080±0.008 | 0.05±0.008 | 0.047±0.008 | 0.02 | 0.023 |  |  |  |  |  |
|                     |             | B          | L C         | I    |       |  |  |  |  |  |



PAD LAYOUT

