

# Power Common Mode choke



## ACMP-4724 Series

Request Samples



Check Inventory



4.7 x 4.5 x 2.4 mm  
RoHS/RoHS II Compliant  
MSL Level = 1

### Features

- Commercial Grade  
Excellent impedance characteristics
- Rated current up to 3.2A
- Extremely Low DCR

### Applications

- DC power line common mode noise suppression.
- Switch Mode Power Supplies and regulators
- Variable Frequency Drives
- AC/DC power rectifiers

### Electrical Specifications

Part Number	Impedance (Ω) @100MHz		DCR (mΩ)	Rated Current (A)	Rated Voltage (Vdc)	Insulation Resistance (MΩ)
	Min	Typ.	Max	Typ.	Max	Min
ACMP-4724-900	30	90	35	3.2	50	10
ACMP-4724-151	80	150	38	3.1	50	10
ACMP-4724-231	180	230	39	3.0	50	10
ACMP-4724-301	180	300	39	3.0	50	10
ACMP-4724-401	200	400	50	2.5	50	10
ACMP-4724-501	300	500	55	2.4	50	10
ACMP-4724-701	500	700	59	2.2	50	10
ACMP-4724-901	700	900	68	2.1	50	10
ACMP-4724-102	800	1000	68	2.1	50	10
ACMP-4724-122	1000	1200	74	2.0	50	10
ACMP-4724-142	1200	1400	81	1.9	50	10

**Rated Current is based on an Irms temperature rise of 40°C.**

**Operating Temperature: -40°C to +125°C. (Including self-heating)**

**Storage (in original packaging): <40°C, <70% RH.**

**ACMP-4724 Series is [RoHS Compliant and Pb free.](#)**

# Power Common Mode choke



## ACMP-4724 Series

Request Samples













Check Inventory



4.7 x 4.5 x 2.4 mm  
**RoHS/RoHS II Compliant**  
 MSL Level = 1

### Electrical Specifications



5101 Hidden Creek Ln Spicewood TX 78669  
 Phone: 512-371-6159 | Fax: 512-351-8858  
 For terms and conditions of sales, please visit:  
[www.abracon.com](http://www.abracon.com)

REVISION: A 08-04-23

ABRACON IS  
 ISO9001-2015  
 CERTIFIED

# Power Common Mode choke




ACMP-4724 Series

Request Samples


Check Inventory

4.7 x 4.5 x 2.4 mm  
**RoHS/RoHS II Compliant**  
 MSL Level = 1

## Mechanical Specifications



A	A1	B	C	D	E	F	G
4.7 ± 0.5	5.2 ± 0.6	4.5 ± 0.5	2.4 MAX	2.7 Ref.	0.75 Ref	1.25 Ref.	1 Ref.



## Recommended Layout

Dimensions: mm

# Power Common Mode choke



**ACMP-4724 Series**

Request Samples




Check Inventory



4.7 x 4.5 x 2.4 mm  
**RoHS/RoHS II Compliant**  
 MSL Level = 1


## Schematic



## Materials

Description	Specification
Core	Ferrite core
Wire	Enameled copper wire
Base	Plastic
Adhesive	Epoxy resin
Terminal	Sn/Cu
Ink	White

## Part Identification



# Power Common Mode choke



ACMP-4724 Series

Request Samples




Check Inventory



4.7 x 4.5 x 2.4 mm  
RoHS/RoHS II Compliant  
MSL Level = 1

## Reflow Profile



Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ 150°C ~ 190°C	60 ~ 120 sec.
2	Reflow	$T_L$ 240°C	20 ~ 40 sec.
3	Peak heat	$T_P$ 260°C Max.	5 sec. Max

1~2 °C/Sec. Ramp

# Power Common Mode choke



**ACMP-4724 Series**

Request Samples





Check Inventory



**4.7 x 4.5 x 2.4 mm**  
**RoHS/RoHS II Compliant**  
**MSL Level = 1**

## Packing

**Tape & Reel: 1000pcs/reel**



W	P	P0	P2	D0	E	F	A0	B0	K0
12 ± 0.30	8.0 ± 0.10	4.0 ± 0.10	2.0 ± 0.10	1.5 ± 0.10	1.75 ± 0.10	5.5 ± 0.10	5.0 ± 0.10	5.2 ± 0.10	2.5 ± 0.10

**Dimensions: mm**

**ATTENTION:** Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669  
 Phone: 512-371-6159 | Fax: 512-351-8858  
 For terms and conditions of sales, please visit:  
[www.abracon.com](http://www.abracon.com)

**REVISION: A 08-04-23**

ABRACON IS  
 ISO9001-2015  
 CERTIFIED