

BU-P3750-@

(Gold-plated Binding Post, Panel Mount)



- The BU-P3750 is a panel mount, gold-plated binding post that accepts unshrouded or retractable 4mm banana plugs, bare wire, or spade plugs.
- Overall length 1.78" (45.2mm), OD = 0.44" (11.2mm)
- Mounts through panels between 0.070" and 0.25" thick with a Ø0.375" (9.52mm) hole.

Material: Contacts Gold-plated brass

Insulator Polycarbonate

• Rating: Current 15 Amps

Voltage Hands-free testing to 2500 VRMS Temperature -50°C (-58°F) to 115°C (239°F)

• Color: The "@" in the model number indicates color.

Available colors: -0 Black, -2 Red

RoHS 3 compliant, exemption 6c

Toll Free: 800.955.2629

Phone: 330.780.2525 Fax: 330.780.2524