


Thick Film Surface Mount Chip Resistors, Wraparound, Extremely Low Value (0.01 Ω to 0.976 Ω)



FEATURES

- Extremely low resistance values (0.01 Ω to 0.976 Ω)
- Suitable for current sensing and shunts
- Metal glaze on high quality ceramic
- Protective overglaze
- Lead (Pb)-free solder contacts on Ni barrier layer
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	CASE SIZE	POWER RATING $P_{70^\circ\text{C}}$ W	TEMPERATURE COEFFICIENT \pm ppm/ $^\circ\text{C}$	RESISTANCE RANGE Ω	TOLERANCE \pm %	E-SERIES ⁽²⁾
RCWH0805	0805	0.33	400	0.010 to 0.018	5.0	24
			300	0.02 to 0.03	1.0, 5.0	24; 96
			200	0.033 to 0.05	1.0, 5.0	
			100	0.051 to 0.976	0.5, 1.0, 5.0 ⁽¹⁾	


Notes

- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material
- Part marking: reference "Surface Mount Resistor Marking" (www.vishay.com/doc?20020)
- ⁽¹⁾ Tight tolerance of 0.5 % is available for resistance values above 0.200 Ω
- ⁽²⁾ Use E24 decade values for 5.0 % tolerance parts and E96 decade values for 0.5 % and 1.0 %. Refer to "Standard Decade" table (www.vishay.com/doc?31001)

GLOBAL PART NUMBER INFORMATION															
Global Part Numbering example: RCWH0805R499FKEA (visit www.vishay.net Vishay Dale parts numbering manual for all options)															
R	C	W	H	0	8	0	5	R	4	9	9	F	K	E	A
GLOBAL MODEL (8 digits)		VALUE (4 digits)				TOLERANCE (1 digit)			TCR (1 digit)			PACKAGING (2 digits)			
RCWH0805		L = mΩ * R = decimal 10L0 = 0.01 Ω R470 = 0.47 Ω Note: * Use "L" for resistance values < 0.1 Ω				D = ± 0.5 % F = ± 1.0 % G = ± 2.0 % J = ± 5.0 %			K = ± 100 ppm/ $^\circ\text{C}$ N = ± 200 ppm/ $^\circ\text{C}$ M = ± 300 ppm/ $^\circ\text{C}$ Q = ± 400 ppm/ $^\circ\text{C}$ P = ± 500 ppm/ $^\circ\text{C}$ T = ± 600 ppm/ $^\circ\text{C}$ G = ± 700 ppm/ $^\circ\text{C}$			EA = lead (Pb)-free, tape / reel			

TECHNICAL SPECIFICATIONS		
PARAMETER	UNIT	RCWH0805
Operating temperature range	$^\circ\text{C}$	-55 to +155
Maximum operating voltage	V	$(P \times R)^{1/2}$
Insulation voltage U_{ins} (1 min)	V	> 200
Insulation resistance	Ω	> 10^9
Weight/1000 pieces (typical)	g	5.5

DIMENSIONS									
RCWH0805									
MODEL	DIMENSIONS in millimeters						SOLDER PAD DIMENSIONS in millimeters		
	RESISTANCE RANGE Ω	L	W	H	T1	T2	a	b	l
RCWH0805	0.01 to 0.03	2.0 ± 0.15	1.3 ± 0.1	0.55 ± 0.1	0.6 ± 0.2	0.35 ± 0.2	1.0	1.4	0.6
	0.033 to 0.976				0.4 ± 0.2		0.8		1.0

DERATING


PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Thermal shock	MIL-STD-202, method 107, -55 °C to +125 °C, 300 cycles at each extreme	± (1.0 % + 0.0005 Ω)
Short time overload	2 x rated power; duration according the model	± (0.5 % + 0.0005 Ω)
High temperature exposure	MIL-STD-202, method 108, 1000 h at T = 125 °C, 0 % power	± (2.0 % + 0.0005 Ω)
Temperature cycling	JESD 22, method JA-104, 1000 cycles (-55 °C to +125 °C)	± (2.0 % + 0.0005 Ω)
Biased humidity	MIL-STD-202, method 103, 1000 h 85 °C/85 % RH, 10 % x (P x R) ^{1/2}	± (2.0 % + 0.0005 Ω)
Mechanical shock	MIL-STD-202, method 213, condition C, 10 g's, 6 ms (half sine), 3 directions	± (1.0 % + 0.0005 Ω)
Vibration	MIL-STD-202, method 204, 5 g's, 20 min, 12 cycles, 3 directions, 10 Hz to 2000 Hz	± (1.0 % + 0.0005 Ω)
Operational life	MIL-STD-202, method 108, 1000 h at T = 125 °C at rated power	± (2.0 % + 0.0005 Ω)
Resistance to solder heat	MIL-STD-202, method 210, +260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± (1.0 % + 0.0005 Ω)
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7a and 7b not required	± (2.0 % + 0.0005 Ω)

PACKAGING					
MODEL	REEL				
	TAPE WIDTH	DIAMETER	PITCH	PIECES/REEL	CODE
RCWH0805	8 mm/punched paper	180 mm/7"	4 mm	5000	EA

Note

- Embossed carrier tape per EIA-481-1A



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.