

www.lemo.com

EPA.00.250.NTN

SUMMARY

Wires

Coax 1



Image is for illustrative purpose only

Series 00

Termination type Female print PCB

IP rating 50

AWG wire size 0.00 - 0.00

Cable Ø 0.00 - 0.00 mm

Status Active

Matching parts FFA.00.250.NTAC29

Download

Request a quote
PCB Eagle Pattern
PCB Altium Pattern
PCB KiCad Pattern

Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model EPA*: Straight receptacle for printed circuit

Keying Circular, female

Housing Material Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces

Weight 3.38 g

Performance

Configuration 00.250 : 1 Coax (50 Ohm)

Insulator T: PTFE Rated Current 4 Amps

Specifications

Contact Type: Coaxial 50 Ohm (Printed Circuit Board)

Contact Dia.: 0.7 mm (0.028in) Test voltage: 2.1 kV (rms)

R (max): 6.1 mOhm

Vtest: 2100 V (AC), 3000 V (DC)

Impedance: 50 Ohm VSWR: 1.09 + 0.11 * f/GHz

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Others

Endurance (Shell): 5000 mating cycles

F ret (min): 100 N

Salt Spray Corrosion: >144 hr

DRAWINGS





Dimensions

	A	L
mm.	7	14
in.	0,28	0,55

RECOMMENDED BY LEMO

Tools

Spanner wrench: Socket for torque wrench DCM.00.M07.4

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.