

www.lemo.com

FFA.3S.275.CTAC72

SUMMARY

Wires

Coax 1



Image is for illustrative purpose only

3S Series

Male solder Coaxial Termination type

IP rating 50

AWG wire size 0.00 - 0.00Cable Ø 5.80 - 7.20 mm

Status Active

Matching parts ERA.3S.275.CTL

Download

Request a quote

Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model FFA*: Straight plug, cable collet

Keying Circular, male

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] **Housing Material**

brass latch sleeve and mid pieces

Weight 55.13 g

Performance

Configuration 3S.275: 1 Coax (75 Ohm)

Insulator T: PTFE **Rated Current** 15 Amps

Specifications

Contact Type: Coaxial 75 Ohm (Solder)

Contact Dia.: 2 mm (0.0787in) Bucket Dia.: 1.8 mm (0.0708in) Vtest: 2700 V (AC), 3900 V (DC)

Impedance: 75 Ohm VSWR: 1.04 + 0.05 * f/GHz

Cable type: RG 213/U, RG 115 A/U, RG 11 A/U, RG 144/U, RG 165 /U

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Others

Endurance (Shell): 5000 mating cycles Temp (min / max): -55°C / +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >144 hr

DRAWINGS



Dimensions

	Α	L	М	S2
mm.	17.8	61	46	14
in.	0,70	2,40	1,81	0,55

RECOMMENDED BY LEMO

Tools

Spanner wrench: DCP.91.023.TN

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

159580	PVC	Black	
62000	PVC	Black	
CCX.50.RG0.58AU61J	PVC	Yellow	
CCX.75.RG0.59BU62N	PVC	Black	
CCX.93.RG0.62AU62N	PVC	Black	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.