



www.lemo.com

SUMMARY

Wires

Coax 1



Image is for illustrative purpose only

Series 00

Termination type Coupler/adapter/bridge

IP rating 50

AWG wire size 0.00 - 0.00

Cable Ø 0.00 - 0.00 mm

Status Active

Download

Request a quote

Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model FTL*: T-plug with two receptacles (90 degree)

Keying Circular (can rotate)

Housing Material Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces

Weight 7.13 g

Performance

Configuration 00.250 : 1 Coax (50 Ohm)

Insulator T: PTFE Rated Current 4 Amps

Specifications

Contact Type: Coaxial 50 Ohm Test voltage: 1.1 kV (rms)

Others


Endurance (Shell): 5000 mating cycles

F ret (min): 100 N

Salt Spray Corrosion: >144 hr

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS





Dimensions

	Α	L
mm.	9	28
in.	0,35	1,10

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.