

9	pecifications	_	Nata		Revision History					
Description	Value	Unit	Notes  1) All dimensions are in mm unless otherwise noted		Version	Description			Date	Approved
Technology	Piezo				1	Released from Engineering			10/21/2013	J.S
Resonant Frequency	2,800	(Hz)	2) All parts meet RoHS							
Rated Voltage	12	(V)								
SPL @ 10cm	106	(dBA)								
Tone	Single Tone									
Mount Type	Flange									
Voltage Range	1.5 ~ 20	(V)								
Max Rated Current	10	(mA)								
Housing Material	ABS				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-20 ~ +60	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Storage Temperature	-30 ~ +70	°C		Piezo Indicator		IP412812-1				
Weight	15	(g)								

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.