





版本	变更内容	工程确认	日期



技术指标 (Technical Index):

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
2. 温度范围 (Temperature range): -25° C ~ +85° C.
3. 额定电压 (Rated voltage): 50V, AC/DC (=等效).
4. 接触电阻 (Contact resistance): ≤0.03 Ω.
5. 绝缘电阻 (Insulation resistance): ≥500M Ω.
6. 产品料号 (Product material No.):

YTC05202-***-***-00
 NO OF CKT (产品PIN数) Plating (电镀方式)
 0: 端子全雾锡 (Terminal all mist tin)
 1: 端子全金 (Terminal G/F OVERALL)
 Packing (包装方式)
 T: TUBE管装
 R: TAPE & REEL卷装



CKT	DIMA	DIMB	DIMC	DIMD
4	1.50	2.56	7.60	5.20
5	2.00	3.06	8.10	
6	2.50	3.56	8.60	
7	3.00	4.06	9.10	
8	3.50	4.56	9.60	
9	4.00	5.06	10.10	
10	4.50	5.56	10.60	
11	5.00	6.06	11.10	
12	5.50	6.56	11.60	
13	6.00	7.06	12.10	
14	6.50	7.56	12.60	
15	7.00	8.06	13.10	
16	7.50	8.56	13.60	
17	8.00	9.06	14.10	
18	8.50	9.56	14.60	
19	9.00	10.06	15.10	
20	9.50	10.56	15.60	
21	10.0	11.06	16.01	
22	10.50	11.56	16.60	
23	11.00	12.06	17.10	
24	11.50	12.56	17.60	
25	12.00	13.06	18.10	
26	12.50	13.56	18.60	
27	13.00	14.06	19.10	
28	13.50	14.56	19.60	
29	14.00	15.06	20.10	
30	14.50	15.56	20.60	
31	15.00	16.06	21.10	
32	15.50	16.56	21.60	

CKT	DIMA	DIMB	DIMC	DIMD
33	16.00	17.06	22.10	5.75
34	16.50	17.56	22.60	
35	17.00	18.06	23.10	
36	17.50	18.56	23.60	
37	18.00	19.06	24.10	
38	18.50	19.56	24.60	
39	19.00	20.06	25.10	
40	19.50	20.56	25.60	
41	20.00	21.06	26.10	
42	20.50	21.56	26.60	
43	21.00	22.06	27.10	
44	21.50	22.56	27.60	
45	22.00	23.06	28.10	
46	22.50	23.56	28.60	
47	23.00	24.06	29.10	
48	23.50	24.56	29.60	
49	24.00	25.06	30.10	
50	24.50	25.56	30.60	
51	25.00	26.06	31.10	
52	25.50	26.56	31.60	
53	26.00	27.06	32.10	
54	26.50	27.56	32.60	
55	27.00	28.06	33.10	
56	27.50	28.56	33.60	
57	28.00	29.06	34.10	
58	28.50	29.56	34.60	
59	29.00	30.06	35.10	
60	29.50	30.56	35.60	

序号 No.	品名 Name	材质 Material
①	0.5拉拔3代胶芯 (H2.0) 0.5 Pitch ZIF Type 3 Housing (H=2.0)	LCP UL94V-0 本色 Natural
②	0.5拉拔下接端子 (H2.0) 0.5 Pitch H2.0 ZIF R/A Type Under terminal	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	0.5拉拔3代后盖 (H2.0) 0.5 Pitch ZIF Type 3 Actuator (H=2.0)	LCP UL94V-0 黑色 Black
④	0.5拉拔3代焊片 (H2.0) 0.5 Pitch ZIF Type 3 Fitting Nail (H=2.0)	铜合金/表面镀锡 Copper Alloy/ Tin Plating

深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD	页码 (SHEET)	1/1	单位 (UNIT): MM
	版本 (REV)	A1	比例 (SCALE)
品名 (ITEM NO)	0.5 Pitch拉拔卧式3代下接 (H=2.0)		一般公差 . ±0.50 .XX ±0.10 .X ±0.20 .XXX ±0.05 ANGLES .X° ±1°
料号 (PART NO)	YTC05202-***-***-LW		
图号 (DWG NO)	日期 (DATE)	2021.10.12	设计 (DESIGN) LUO 审核 (CHECKED) ROGER LI 核准 (APPROVED) ROC ZHAO

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd. The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd. Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com