

SUMMARY

Wires

Triax 1

Image is for illustrative purpose only

00 **Series**

Female solder Termination type

IP rating 50

AWG wire size 0.00 - 0.00 Cable Ø 0.00 - 0.00 mm

Status Active

Matching parts FFC.00.650.CLAC31

Download

Request a quote

Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model ERN*: Fixed receptacle, nut fixing, with earthing tags

Keying Circular, female

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] **Housing Material**

brass latch sleeve and mid pieces

Weight 2.61 g

Performance

Configuration 00.650: 1 Triax (50 Ohm) Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 3 Amps

Specifications

Contact Type: Triaxial 50 Ohm (Solder)

Contact Dia.: 0.5 mm (0.02"in) Vtest: 1200 V (AC), 1700 V (DC)

Impedance: 50 Ohm VSWR: 1.1 + 0.11 * f/GHz


Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): 5000 mating cycles

Salt Spray Corrosion: >1000 hr

DRAWINGS





Dimensions

	Α	L
mm.	8	15
in.	0,31	0,59

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.