XS1M18KPM40

Inductive proximity sensors XS, inductive sensor XS1 M18, L60mm, brass, Sn5mm, 12...24 VDC, cable 2 m





Main

Range of Product	Telemecanique Inductive proximity sensors XS
Series name	Application
Sensor Type	Inductive proximity sensor
Device Application	Factor 1 (Fe/Nfe)
Sensor name	XS1
Sensor design	Cylindrical M18
Size	60 mm
Body type	Fixed
Detector flush mounting acceptance	Flush mountable
Material	Metal
Enclosure Material	Nickel Plated Brass
Type of output signal	Discrete
Wiring Technique	4-wire
[Sn] nominal sensing distance	0.20 in (5 mm)
Discrete output function	1 NO or 1 NC programmable
Output circuit type	DC
Discrete output type	PNP and NPN
Electrical connection	Cable
Cable length	6.56 ft (2 m)
[Us] rated supply voltage	1224 V DC reverse polarity protection
Switching capacity in mA	<= 200 mA overload and short-circuit protection
IP degree of protection	IP68 conforming to IEC 60529

Complementary

Complementary	
Thread type	M18 x 1
Detection face	Frontal
Front material	PPS
Operating zone	0.000.16 in (04 mm)
Differential travel	115% of Sr
Repeat accuracy	3% of Sr
Cable composition	4 x 0.34 mm²
Wire insulation material	PvR
Status LED	Output state 1 LED yellow)
Supply voltage limits	1038 V DC
Switching frequency	<= 1000 Hz
Maximum voltage drop	<2.6 V closed)
Current consumption	015 mA no-load
Maximum delay first up	10 ms
Maximum delay response	0.3 ms
Maximum delay recovery	0.7 ms
Marking	CE
Threaded length	2.05 in (52 mm)

Ordering and shipping details Category	22486-SENSORS, PROXIMITY	
	CSA	
Product Certifications	UL	
Environment		
Net Weight	0.26 lb(US) (0.12 kg)	
Length	2.36 in (60 mm)	
Height	0.71 in (18 mm)	

0 11 0	
Category	22486-SENSORS, PROXIMITY
Discount Schedule	DS2
GTIN	3389110653236
Nbr. of units in pkg.	1
Package weight(Lbs)	4.27 oz (121.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE	
Package 1 Height	1.65 in (4.2 cm)	
Package 1 width	3.74 in (9.5 cm)	
Package 1 Length	5.12 in (13 cm)	
Unit Type of Package 2	S01	
Number of Units in Package 2	11	
Package 2 Weight	3.33 lb(US) (1.511 kg)	
Package 2 Height	5.91 in (15 cm)	
Package 2 width	5.91 in (15 cm)	
Package 2 Length	15.75 in (40 cm)	

Offer Sustainability


Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EPEU RoHS Declaration
Mercury free	Yes
RoHS exemption information	€Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

14/	40
vvarranty	18 months

XS1M18KPM40


Dimensions



XS1M18KPM40


Minimum Mounting Distances

Side by side




e (1) ≥ 10 mm/0.39 in.

Face to face




e (2) ≥ 60 mm/2.36 in. Facing a metal object



e (3) ≥ 15 mm/0.60 in

Mounting




(1) Bending cable: 4 x external cable diameter

Product data sheet Connections and Schema

XS1M18KPM40

Wiring Schemes

4-Wire DC, PNP/NPN, NO or NC Output




BU : Blue BN : Brown BK : Black WH : White

Product data sheet Performance Curves

XS1M18KPM40

Performance Curves

Standard Steel Target: 18x18x1 mm



- (1) Pick-up points
- (2) Drop-out points (object approaching from the side)
- (y) Sensing distance in mm