




③ 2.54 ± 0.20



④ 2.54 ± 0.20



② 3.0 ± 0.30



Recommended PCB Layout

NOTE:

MATERIAL

HOUSING: PA6T BK UL94V-0.

CONTACT: Brass.

CONTACT PLATING: GOLD .

ELECTRICAL

CURRENT RATING: 3AMP.

VOLTAGE RATING: 250VAC/DC.

DIELECTRIC WITHSTANDING VOLTAGE: 600VAC MIN.

CONTACT RESISTANCE: 20mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN.

ENVIRONMENTAL

TEMPERATURE RANGE: -40° C TO +105° C.

DIMENSION TABLE 注: 1x40P A尺寸不用減去0.25mm

Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
1 x 2	5.08	2.54	1 x 15	38.10	35.56	1 x 28	71.12	68.58
1 x 3	7.62	5.08	1 x 16	40.64	38.10	1 x 29	73.66	71.12
1 x 4	10.16	7.62	1 x 17	43.18	40.64	1 x 30	76.20	73.66
1 x 5	12.70	10.16	1 x 18	45.72	43.18	1 x 31	78.74	76.20
1 x 6	15.24	12.70	1 x 19	48.26	45.72	1 x 32	81.28	78.74
1 x 7	17.78	15.24	1 x 20	50.80	48.26	1 x 33	83.82	81.28
1 x 8	20.32	17.78	1 x 21	53.34	50.80	1 x 34	86.36	83.82
1 x 9	22.86	20.32	1 x 22	55.88	53.34	1 x 35	88.90	86.36
1 x 10	25.40	22.86	1 x 23	58.42	55.88	1 x 36	91.44	88.90
1 x 11	27.94	25.40	1 x 24	60.96	58.42	1 x 37	93.98	91.44
1 x 12	30.48	27.94	1 x 25	63.50	60.96	1 x 38	96.52	93.98
1 x 13	33.02	30.48	1 x 26	66.04	63.50	1 x 39	99.06	96.52
1 x 14	35.56	33.02	1 x 27	68.58	66.04	1 x 40	101.60	99.06

RoHS2.0

本圖紙知識產權及版權由深圳市永豐盈電子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的權利。

類別	HEADER	品名	CS-1110-30 L=10.1 6T	X.	±0.50	材料		單位	mm	SHEET 1 OF 1	
版本	A/0	設計	李文暢	X.X	±0.20	顏色		比例	1:1	▲	修改內容
制定部門	工程部	繪製	李文暢	X.XX	±0.10	畫法	⊕	數量		①	
工程圖號	CST-1110	審核	姚培柱	X.XXX	±0.05	CST 深圳市永豐盈電子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.					
制定日期	2020/5/22	核准	周中湖	X.XXXX	±0.01						

③		
④		
⑤		
⑥		
⑦		
⑧		