

12G SDI 75 Ohm HD-BNC Female Bulkhead Mount Connector Solder Attachment 0.062" PCB



RF Connectors Technical Data Sheet

PE40015

Configuration

- HD-BNC Female Connector
- 75 Ohms
- · Straight Body Geometry

Features

- · Max. Operating Frequency 12 GHz
- Gold Plated Brass Contact
- 10 µin minimum contact plating
- Meets SMPTE ST 2082-1
- Backwards Compatible with 2081-1

Applications

- General Purpose Test
- Rack and Panel Mount Applications
- PCB Applications

- 12G-SDI, Video, and Broadband UHDTV
- Broadband Internet Delivery
- Broadcast A/V

- Connector Interface Types: 0.062" Board Thickness
- Bulkhead
- 12Gb/s Transmission
- Cost Effective
- 4x Panel Density of Standard BNC
- 20% Lighter than Standard BNC
 - 4K/8K Video Equipment
 - Medical Equipment Requiring High Speed Video
 - HD Cameras

Description

Pasternack's PE40015 75 ohm HD-BNC female bulkhead connector with solder attachment for 0.062" Board Thickness PCB is part of our full line of RF components available for same-day shipping. Our HD-BNC female connector operates up to a maximum frequency of 12 GHz. This HD-BNC bulkhead connector allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. Pasternack's 12G-SDI HD-BNC connector PE40015 utilizes 12Gb/s data transfer rates to enable high resolution uncompressed video signal transmission. These products offer 4K and Ultra-HD quality signals that meet SMPTE ST 2082-1. These 75 Ohm connectors are available in PCB edge-mount, straight, or right angle configurations, as well as coaxial connectors to be used in industry standard cable assemblies.

Our 75 ohm HD-BNC female bulkhead connector PE40015 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12	GHz

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 12G SDI 75 Ohm HD-BNC Female Bulkhead Mount Connector Solder Attachment 0.062" PCB PE40015

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



12G SDI 75 Ohm HD-BNC Female Bulkhead Mount Connector Solder Attachment 0.062" PCB



RF Connectors Technical Data Sheet

PE40015

Mechanical Specifications

Size

 Length
 0.689 in [17.5 mm]

 Width/Dia.
 0.3 in [7.62 mm]

 Height
 0.3 in [7.62 mm]

 Weight
 0.05 lbs [22.68 g]

Material Specifications

Description	Material	Plating
Contact	Brass	Gold 10 μin minimum
Insulation	PTFE	
Outer Conductor	Brass	Nickel 100 µin minimum
Body	Brass	Nickel 100 μin minimum

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 12G SDI 75 Ohm HD-BNC Female Bulkhead Mount Connector Solder Attachment 0.062" PCB PE40015

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



12G SDI 75 Ohm HD-BNC Female Bulkhead Mount Connector Solder Attachment 0.062" PCB



RF Connectors Technical Data Sheet

PE40015

12G SDI 75 Ohm HD-BNC Female Bulkhead Mount Connector Solder Attachment 0.062" PCB from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 12G SDI 75 Ohm HD-BNC Female Bulkhead Mount Connector Solder Attachment 0.062" PCB PE40015

URL: https://www.pasternack.com/hd-bnc-female-pcb-connector-pe40015-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE40015 CAD Drawing

12G SDI 75 Ohm HD-BNC Female Bulkhead Mount Connector Solder Attachment 0.062" PCB

