



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS
 Current Rating:2.0AMP
 Contact Resistance:20mΩ Max
 Dielectric Strength:Min 1000V RMS
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PPS
 Soldering Temperature: 260°C±5° 5S

Ordering Information

PZ 200 - * - N - Z - ** - C

- No.of Rows
1=Single Row
2=Dual Row
- No.of Pins
2-40Pin
- Type
Z=直排针
R=弯排针
S=插板
- Contact Plating
C0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin
- Round Pin
(圆针)

			GENREL TOLERANCE		制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM	TOL	审 核 CHECK		产品名称 TITLE		2.0 单排 直排针 塑高3.0 (上针0.5 下针0.5)	版本 REV.	A
			X. X	±0.30	批 准 APPROVAL		产品料号 PART NO.		PZ200-1-N-Z-XX-C	单 位 UNITS	mm
1			初版发行		比 例 SCALE					页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投 影 Projection	材料 MATERIAL					