


SPECIFICATIONS

- 1、Current Rating: 9A AC, DC
- 2、Voltage Rating: 600V AC, DC
- 3、Temperatuer Range: -25°C~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
1	HC-5557-2x1A	---	5.40
2	HC-5557-2x2A	4.20	9.60
3	HC-5557-2x3A	8.40	13.80
4	HC-5557-2x4A	12.60	18.00
5	HC-5557-2x5A	16.80	22.20
6	HC-5557-2x6A	21.00	26.40
7	HC-5557-2x7A	25.20	30.60
8	HC-5557-2x8A	29.40	34.80
9	HC-5557-2x9A	33.60	39.00
10	HC-5557-2x10A	37.80	43.20
11	HC-5557-2x11A	42.00	47.40
12	HC-5557-2x12A	46.20	51.60

PCB LAYOUT

			GENREL TOLERANCE		制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK					
			X.X	±0.30	批 准 APPROVAL		产品名称 TITLE	4.20双排直针	版本 REV.	A
			X.XX	±0.20	比 例 SCALE		产品料号 PART NO.	HC-5557-2xNA	单 位 UNITS	mm
			X.XXX	±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle	±3.0°						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE								
1	初版发行									