



Specifications:
 规格:
 Voltage rating: 100V AC/DC
 额定电压: 100V AC/DC
 Current rating: 3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage: 1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range: -40°C ~ +85°C
 温度范围: -40°C ~ +85°C
 Insulation resistance: 1000MΩ min
 绝缘电阻: 1000MΩ Min
 Contact resistance: 20mΩ Max
 接触电阻: 20mΩ Max

K 205001 H F - XX - PT
 ① ② ③ ④ ⑤ ⑥

- 1.K-XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:F-Female Housing
- 5.Row No.Pin No:XX-02~04 Pin
- 6.Material:PT-PBT

Poles	Dimensions(mm)	
	A	B
02	2.00	7.00
03	4.00	9.00
04	6.00	11.00

K205001HF-XX-PT	PBT	K205001HM	K205001TM
PART NO	Material	Suitable XKB Housing	Suitable XKB Terminal

DSND	SCALE: N/A	MODEL TYPE: 2.0mm automotive connector
DWN	VIEW:	PART NO.: K205001HF-XX-PT
CHKD	UNIT: mm/in	DWG NO.: X-K205001HF-XX-PT
APPD	SIZE: A4	

XKB

XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR $\pm 5^\circ$
ΔX					$L \leq 4$ ± 0.2
ΔX					$4 < L \leq 16$ ± 0.3
					$16 < L \leq 63$ ± 0.4
					$L > 63$ ± 0.5

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn