



## PCB LAYOUT

- SPECIFICATIONS**
- 1、Current Rating: 7A AC, DC
  - 2、Voltage Rating: 600V AC, DC
  - 3、Temperature Range: -25°C~+85°C
  - 4、Contact Resistance: 20mΩ Max
  - 5、Insulation Resistance: 1000MΩ Min
  - 6、Withstanding Voltage: 1500V AC/minute
  - 7、Material: Wafer Nylon66, UL94V-0  
PIN Brass Tin-plated

编号	尺寸 (mm)	
	A	B
2x1AW	4.20	5.40
2x2AW	8.40	9.60
2x3AW	12.60	13.80
2x4AW	16.80	18.00
2x5AW	21.00	22.20
2x6AW	25.20	26.40
2x7AW	29.40	30.60
2x8AW	33.60	34.80
2x9AW	37.80	39.00
2x10AW	42.00	43.20
2x11AW	46.20	47.40
2x12AW	50.40	51.60

制图	变更内容	日期	GENERAL TOLERANCE		制图	钱岳生	料号
DRAWING	DESCRIPTION	DATE	X.±0.25	X.±2°	DRAWING	2021、05、03	HC-5557-4、2-2x3AW
			X.±0.20	X.±1°	审核	张名	品名
			.XX±0.15	.XX±0.5°	CHECK	2021、05、04	5557双排弯针
			.XXX±0.10	.XXX±0.5°	核准	张名	TITLE
					APPROVAL	2021、05、05	客户料号
					UNIT	MM	CITM. NO.
					SCALE	1:1	

深圳市虹成电子有限公司