



PCB LAYOUT

- SPECIFICATIONS**
- Current Rating: 7A AC, DC
 - Voltage Rating: 600V AC, DC
 - Temperature Range: -25°C~+85°C
 - Contact Resistance: 20mΩ Max
 - Insulation Resistance: 1000MΩ Min
 - Withstanding Voltage: 1500V AC/minute
 - Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编号	尺寸 (mm)	
	A	B
2x1A	4.20	5.40
2x2A	8.40	9.60
2x3A	12.60	13.80
2x4A	16.80	18.00
2x5A	21.00	22.20
2x6A	25.20	26.40
2x7A	29.40	30.60
2x8A	33.60	34.80
2x9A	37.80	39.00
2x10A	42.00	43.20
2x11A	46.20	47.40
2x12A	50.40	51.60

制图	变更内容	日期	GENERAL TOLERANCE	
DRAWN	DESCRIPTION	DATE	X.±0.25	X.±2°
			X.±0.20	X.±1°
			.XX±0.15	.XX±0.5°
			.XXX±0.10	.XXX±0.5°

制图	钱岳生
DRAWING	2021.05.03
审核	张名
CHECK	2021.05.04
核准	张名
APPROVAL	2021.05.05

料号	HC-5557-4.2-2x5A	版本	A
PART NO.	5557双排直针	REV.	1/1
品名	5557双排直针	页次	1/1
TITLE	客户料号	SHEET	1/1
CITM. NO.			

深圳市虹成电子有限公司