




(1)





.XX ±0.13 .XXX ±0.10




NOTES:

MATERIAL:

HOUSING:GREEN THERMOPLASTIC POLYESTER, UL94V-0SHELL:STEEL, TIN PLATEDCONTACT:COPPER ALLOY, 30µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

628 SERIES D-SUB CONNECTOR		SW REFERENCE NO.: 628M ASSEMBLY		
		DRAWN: C.B	DATE: AUG. 01/2	018
		CHECKED:	DATE:	DATE:
EDAC INC TORONTO, ONTARIO YOUR CONNECTION TO QUALITY & SERVICE	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1	SHEET 1 OF	1
		DRAWING NUMBER: 628-M37-621-GT2		ISSUE
		PART NUMBER: 628-M	37-621-GT2	1





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.