


10.7 ±0.3 5.80 5.1 ±0.3

.XX ±0.13 .XXX ±0.10



NOTES:

MATERIAL:

HOUSING: GREEN THERMOPLASTIC POLYESTER, UL94V-0 STEEL, TIN PLATED SHELL: CONTACT: COPPER ALLOY, 30µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

CURRENT RATING: 5A PER CONTACT $25m\Omega$ MAX. CONTACT RESISTANCE: INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC rms

	SW REFERENCE NO.: 628M ASSEMBLY					
628 SERIES D-SUB CONNECTOR		DRAWN: C.B		DATE: AUG. 01/2018		018
		CHECKED:		DATE:		
EDAC INC TORONTO, ONTARIO CANADA	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1		SHEET	1 OF	1
		DRAWING NUMBER: 6	BER: 628-M37-621-GT6			ISSUE
YOUR CONNECTION TO QUALITY & SERVICE		PART NUMBER: 6	628-M37-6	621-GT6		1



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

