



| TOLERANCE<br>UNLESS OTHERWISE<br>SPECIFIED |       |  |  |
|--|-------|--|--|
| .X   | ±0.25 |  |  |
| .XX  | ±0.13 |  |  |
| .XXX                                       | ±0.10 |  |  |

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER ORIGINAL





## NOTES:

MATERIAL:

HOUSING: GREEN THERMOPLASTIC POLYESTER, UL94V-0

SHELL: STEEL, NICKEL PLATED

CONTACT: COPPER ALLOY, GOLD FLASH PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

**CURRENT RATING: 5A PER CONTACT** 

**CONTACT RESISTANCE:**  $25m\Omega$  MAX. INSULATOR RESISTANCE: 5000MΩ min.

**DIELECTRIC** 

WITHSTANDING VOLTAGE: 1000V AC rms

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.





EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

| SCALE: 1:1            | SHEET 1 OF 1       |
|-----------------------|--------------------|
| CHECKED:              | DATE:              |
| DRAWN: C.B            | DATE: AUG. 01/2018 |
| SW REFERENCE NO.: 628 | M ASSEMBLY         |

628-M50-221-GN5 **ISSUE** DRAWING NUMBER: PART NUMBER: 628-M50-221-GN5