


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.

ISSUE NUMBER ORIGINAL







NOTES:

MATERIAL: HOUSING: DIALLYL PTHYHALATE, UL94V-0 CONTACT MATERIAL: COPPER ALLOY CONTACT PLATING: GOLD PLATING OVER NICKEL 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT INSERTION FORCE: WITHDRAWAL FORCE: 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT

OPERATING TEMPERATURE: -65°C ~ 125°C

CURRENT RATING: **10A PER CONTACT** CONTACT RESISTANCE: $10m\Omega$ MAX. INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 2000V AC rms AT SEA LEVEL

CONTACT TYPE: 542-Wire Wrap .050x.025(1.27x0.61) - Tail LG.=.790(20.07)

| | | · · · · · · · · · · · · · · · · · · · | | | |
|--------------------------------|--------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|---------------------------------|------------------|-------|
| | 415 & 438 SERIES CARD EDGE | | SW REFERENCE NO.: 415 ASSEMBLY | | |
| | | | DRAWN: W.T | DATE: AUG. 01/20 |)18 |
| | | | CHECKED: | DATE: | |
| CONFORMS TO | EDAC INC | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INCAND | SCALE: 1:1 | SHEET 1 OF | 1 |
| DN DIRECTIVES S COMPLIANCY. | YOUR CONNECTION TO QUALITY & SERVICE | SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | DRAWING NUMBER: 415-047-542-112 | | ISSUE |
| | | | PART NUMBER: 415-047-5 | 542-112 | 1 |



THIS SERIES FULLY COI THE EUROPEAN UNION 2011/65/EU FOR RoHS (