<u>Contact Dimensions:</u>
524-P.C. Tail .018 Sq.(0.46 Sq.) - Tail LG=.175(4.45)
.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing 1 -2x Ø.156[3.96] 6.900 175.26 7.060 179.32 7.375 187.33 .330[8.38] CARD SLOT 160[4.06] POINT OF CONTACT FORCE SECTION A-A 600 [15.24] 250 [6.35] -7.635 [193.93] 345-ENG-MASTER 345/395 SERIES CARD EDGE CONNECTOR DRAWN: R.STA.MONICA DATE:MAY.16/2017 PART NUMBER: 395-068-524-403 INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0 1:1 SHEET 1 OF 2 CONTACT MATERIAL; COPPER TIN ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING

YOUR CONNECTION TO QUALITY & SERVICE

345-ENG-MASTER

ON THE CONTACT TAILS, NICKEL UNDERPLATE









**Contact Code 558** 

Contact Code 559

**Contact Code 560** 

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0 DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2 345-ENG-MASTER