

	12	11	10		9	8	7	6		5	4	3 2	2	
LOOSE PIECE			TAPE MOUNTED		SPECIFICATIONS									
Н	MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.	"I.D." MIN.	"H"	STOCK ±.001 [0.025] THICKNESS		
	190540032	A-220-04X			4	.119 [3.02]	00E [E 74]	457 [2 00]	750 [40 20]	060 [4 57]	00 [04 00]	020 [0.74]		
	190540033	A-220-06X			6	.146 [3.71]	.225 [5.71]	.157 [3.99]	.759 [19.28]	.062 [1.57]	.98 [24.89]	.028 [0.71]		
	190540035	A-221-06X			6	.146 [3.71]								
	190540037	A-221-08X	190540038	A-221-08XT	8	.173 [4.39]	.312 [7.92]	.270 [6.86]	.946 [23.26]	.062 [1.57]	.98 [24.89]	.028 [0.71]		
G	190540039	A-221-10X	190540040	A-221-10XT	10	.198 [5.03]								
	190540042	A-222-14X			14	.265 [6.73]	467 [44 96]	206 [0 00]	1 110 [20 10]	062 [4 57]	00 [24 90]	029 [0.74]		
	190540044	A-222-56X			56	.328 [8.33]	.467 [11.86]	.386 [9.80]	1.110 [28.19]	.062 [1.57]	.98 [24.89]	.028 [0.71]		
	190540048	A-226-38X			38	.390 [9.91]	.534 [13.56]	.552 [14.02]	1.309 [33.25]	.054 [1.37]	1.172 [29.77]	.031 [0.79]		
	190540051	A-232-04X			4	.119 [3.02]								
F	190540052	A-232-06X	190540053	A-232-06XT	6	.146 [3.71]	.254 [6.45]	.240 [6.10]	.857 [21.77]	.062 [1.57]	.98 [24.89]	.028 [0.71]		
	190540054	A-232-08X			8	.173 [4.39]								
E														
D				-	_ "L"	•								



NOTES:

- 1. MATERIAL:
 - (A). RING TONGUE TERMINAL: COPPER PLATING: ELECTRO-TIN (.0003 MIN.)
 - (B). INSULATION: MOLDED PVC (RED)
- 2. MWID: MAXIMUM WIRE INSULATION DIAMETER
- 3. WIRE SIZE: 22 -18 AWG
 - .25 -1.5 MM²
- 4. ALL DIMENSIONS IN INCHES/[MM].
- 5. PARTS ARE ROHS COMPLIANT.
- 6. DIMS. SHOWN ARE FOR REFERENCE ONLY.

DOCUMENT STATUS P1 RELEASE DATE 2022/11/29 12:44:59



PARTS ON TAPE

DIMENSION UNITS SCALE INCH NTS			NT REV DESC: (PCN#512131	OBSOLETED PA	NOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION MOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								
_	AL TOLERA	-						-					
	MM	INC		707770		RING TONGUE TERMINAL							
4 PLACES ± ±				EC NO: 727779 DRWN: ANIKES1 2022/09/30				INSULKRIMP 200-SERIES					
3 PLACES ± ± 0.005			05	ANIKES1									
			CHK'D:	CHK'D: GGA 2022/11/29									
		APPR:	APPR: GGA 2022/11/29			PRODUCT CUSTOMER DRAWING							
1 PLACE	1 PLACE ± 0.25 ±		INITIA	L REVISION:			DOCUMENT NUMBER				DOC TYPE	DOC PART RE	REVISION
0 PLACES ± ±		DRWN:	ABENJAMIN	LW	2019/08/23	190540031			PSD	DOD	000 0	۸ ၁	
		APPR:	JMACNEIL		2019/09/05		1905	40031	JU3 I		000 A	A3	
DRAFT WHERE APPLICABLE			THIRD AN	THIRD ANGLE PROJECTION DRAWING			MATERIAI	NUMBER CUSTOMER				SHEET NUMBER	
MUST REMAIN WITHIN DIMENSIONS					C-SIZE	19054	SE	E TABLE	GENER	AL MARKET 1 OF)F 1	
5			•	4		3		2		1			