
Contact Dimensions: 540-Wire Wrap .025 Sq.(0.64 Sq.) - Tail LG=.560(14.22) .100 (2.54) Contact Spacing x .200 (5.08) Row Spacing



1

-3.400 [86.36] 3.560 90.42



.160[4.06] POINT OF CONTACT .330[8.38] CARD SLOT 150 [3.81] SECTION A-A

345/395 SERIES CARD EDGE CONNECTOR PART NUMBER: 395-033-540-101

YOUR CONNECTION TO QUALITY & SERVICE

	DRAWN: R.STA.MONICA	DATE: MA	Y.16/2017
	CHECKED:	DATE:	
	SCALE: 1:1	SHEET '	OF 2
0	DRAWING NUMBER		ISSUE
	345-ENG-MASTER		1

ACAD REFERENCE NO. 345-ENG-MASTER

INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0

CONTACT MATERIAL; COPPER TIN ALLOY

CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE









Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2 345-ENG-MASTER