


J

COMPLIANT

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



NOTES:

MATERIAL: HOUSING: DIALLYL PTHYHALATE, UL94V-0 CONTACT MATERIAL: COPPER ALLOY CONTACT PLATING: GOLD PLATING OVER NICKEL 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT INSERTION FORCE: WITHDRAWAL FORCE: 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT

OPERATING TEMPERATURE: -65°C ~ 125°C

CURRENT RATING: **10A PER CONTACT** CONTACT RESISTANCE: 10mΩ MAX. INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 2000V AC rms AT SEA LEVEL

CONTACT TYPE: 540-Wire Wrap .050x.024(1.27x0.61) - Tail LG.=.600(15.24)

			SW REFERENCE NO.: 415 ASSEMBLY		
415 & 438 SERI		CARD EDGE	DRAWN: W.T	DATE: AUG. 01/20	018
THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.			CHECKED:	DATE:	
	EDAC INC TORONTO, ONTARIO CANADA	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1	SHEET 1 OF	1
			DRAWING NUMBER: 415-035-	540-212	ISSUE
			PART NUMBER: 415-035-540-212		1