

SPECIFICATIONS	
Rating:	100 mA @ 16 VDC
Life Expectancy:	10,000 cycles typical
Contact Resistance:	50 mΩ initial @ 2-4 VDC, 100mA
Dielectric Strength:	1,000 max V rms at sea level
Insulation Resistance:	100 MΩ min.
Operating Force:	0.5 N/cm

MATERIALS	
Cover:	Stainless steel
Contact:	Silver-plated copper alloy
Terminals:	Silver-plated copper alloy

FEATURES & BENEFITS


- ▶ 9-position rotary
- ► Thru-hole termination
- ► Positive detents

APPLICATIONS/MARKETS

- ► Industrial controls
- ► Test & instrumentation
- ► Appliance
- ► HVAC



HOW TO ORDER




Example Ordering Number


KC-1901-A


Specifications subject to change without notice.


KC

1901









235