


PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material:Wafer Nylon46,UL94V-0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-1.25-2AW-X	1.25	4.25
3	HC-1.25-3AW-X	2.50	5.50
4	HC-1.25-4AW-X	3.75	6.75
5	HC-1.25-5AW-X	5.00	8.00
6	HC-1.25-6AW-X	6.25	9.25
7	HC-1.25-7AW-X	7.50	10.50
8	HC-1.25-8AW-X	8.75	11.75
9	HC-1.25-9AW-X	10.00	13.00
10	HC-1.25-10AW-X	11.25	14.25
11	HC-1.25-11AW-X	12.50	15.50
12	HC-1.25-12AW-X	13.75	16.75
13	HC-1.25-13AW-X	15.00	18.00
14	HC-1.25-14AW-X	16.25	19.25
15	HC-1.25-15AW-X	17.50	20.50
16	HC-1.25-16AW-X	18.75	21.75

Ordering Information



		GENERAL TOLERANCE		制图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
		DIM	TOL	DRAWING				
		X.X	±0.30	审核	产品名称	1.25 弯针	版本	A
		X.XX	±0.20	CHECK	TITLE		REV.	
		X.XXX	±0.10		批准		UNIT	mm
1	初版发行	日期		APPROVAL	产品料号	HC-1.25-NAW-X	UNITS	
序号	变更内容	日期		SCALE	PART NO.		SHEET	1/1
No.	MODIFY CONTENT	MODIFY DATE		Angle	±3.0°	材料		
				投影	Projection			