










REV.	ECN. NO.	APPD.
A		
REV.	ECN. NO.	APPD.
①	品名	材质
②	1.0 K型立式端子 (H2.5)	1.0 K型端子 (H2.5)
③	1.0 K型立式后盖 (H2.5)	1.0 K型立式后盖 (H2.5)
④	1.0 K型立式焊片 (H2.5)	1.0 K型立式焊片 (H2.5)



CKT	DIM A	DIM B	DIM C
4	3.00	5.03	11.10
5	4.00	6.03	12.10
6	5.00	7.03	13.10
7	6.00	8.03	14.10
8	7.00	9.03	15.10
9	8.00	10.03	16.10
10	9.00	11.03	17.10
11	10.00	12.03	18.10
12	11.00	13.03	19.10
13	12.00	14.03	20.10
14	13.00	15.03	21.10
15	14.00	16.03	22.10
16	15.00	17.03	23.10
17	16.00	18.03	24.10
18	17.00	19.03	25.10
19	18.00	20.03	26.10
20	19.00	21.03	27.10
21	20.00	22.03	28.10
22	21.00	23.03	29.10
23	22.00	24.03	30.10
24	23.00	25.03	31.10
25	24.00	26.03	32.10
26	25.00	27.03	33.10
27	26.00	28.03	34.10
28	27.00	29.03	35.10
29	28.00	30.03	36.10
30	29.00	31.03	37.10
31	30.00	32.03	38.10
32	31.00	33.03	39.10
33	32.00	34.03	40.10
34	33.00	35.03	41.10
35	34.00	36.03	42.10
36	35.00	37.03	43.10
37	36.00	38.03	44.10
38	37.00	39.03	45.10
39	38.00	40.03	46.10
40	39.00	41.03	47.10

技术指标:  
 1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。  
 2. 温度范围: -25°C~85°C。  
 3. 额定电压: 50V, AC/DC(等效)。  
 4. 接触电阻: ≤0.03Ω。  
 5. 绝缘电阻: ≥500MΩ。  
 6. 产品料号:  
 LL10553-XX X X

NO OF CKT (产品PIN数)  
 Plating(电镀方式)  
 O: 端子全雾锡  
 T: 端子全镀(G/F)  
 OVERALL)

Packing(包装方式)  
 R: TUBE 管装  
 C: TAPE & REEL WITH COVER 吸盘卷装

X.	±0.30	X°	±5°	UNITS	mm
.X	±0.20	.X°	±2°	MATL	
.XX	±0.10	.XX°	±1°		
.XXX ±0.05	.XXX° ±0.5°			FINISH	

NAME(INTENDED USE)		TITLE:	
PART NO.(INTENDED USE)		MINTRON CO.,LTD.	
APPD:	SUNNY	DWG NO.:	LL10553-XXXX
CHKD:	LISA	SCALE	1/1
DR:	ZOE	SHEET	1/1
	2015-12-10	REV.	A