


NOTES:

MATERIAL:

HOUSING:GREEN THERMOPLASTIC POLYESTER, UL94V-0SHELL:STEEL, NICKEL PLATEDCONTACT:COPPER ALLOY, 30µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

	628 SERIES D-SUB CONNECTOR		SW REFERENCE NO.: 628M ASSEMBLY		
			DRAWN: C.B	DATE: AUG. 01/20)18
			CHECKED:	DATE:	
	EDAC INC	OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS	SCALE: 1:1	SHEET 1 OF	1
	EDAC INC TORONTO, ONTARIO CANADA		DRAWING NUMBER: 628-M25	MBER: 628-M25-621-GN5	
	YOUR CONNECTION TO QUALITY & SERVICE		PART NUMBER: 628-M25	-621-GN5	1





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.